



## Short drill chuck Form A, HSK-A 100, Clamping range: 0,5-13mm



### Order data

Order number	307760 0,5-13
GTIN	2050001690043
Item class	33W

### Description

#### Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

#### Supplied with:

Clamping wrench with T-handle.

#### Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

### Technical description

Type	standard
Overhang dimension A	111 mm
Spare chuck key No. 627425	6 AF
Clamping range	0.5 - 13 mm
External Ø D	50 mm
Adapter	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 μm
maximum tightening torque $M_{d\ max}$	≤ 14 Nm
Type of product	Short drill chuck

---

## Accessories

Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
---	----------