

**Short taper chuck flange DIN 55027, Ø d1 / taper: 315/8mm****Order data**

Order number	317500 315/8
GTIN	4019208033549
Item class	33R

Description**Version:**

Finish machined on all sides.

Application:

For retrofitting to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

Material:

C45 steel

Technical description

Thickness B	26 mm
Taper Ø d ₂	139.735 mm
Number of studs	4
External Ø d ₁	315 mm

Taper size	8
Type of product	Lathe chuck accessories