



Flange blank for geared scroll chuck, External Ø D: 135 mm



Order data

Order number	317000 135
GTIN	4019208002965
Item class	33R

Description

Version:

Cleanly cast, unmachined, shot blasted, large allowance.

Application:

Attachment of **chucks with recessed mount to DIN 6350 to spindle noses DIN 800**. The adaptor plate blank must be machined and fitted to the machine and chuck.

Material:

Cast iron

Suitable for :

Three-jaw lathe chuck No. 310100; 310500, four-jaw lathe chuck **No. 312000; 312500** and combi lathe chuck **No. 315630**.

suitable for chuck Ø: 125 mm

Collar Ø d₂: 80 mm

Bore Ø d₃: 25 mm

Height h₁: 58 mm

Flange thickness h₂: 20 mm

Technical description

External Ø D	135 mm
--------------	--------

Bore $\varnothing d_3$	25 mm
suitable for chuck \varnothing	125 mm
Collar $\varnothing d_2$	80 mm
Height h_1	58 mm
Flange thickness h_2	20 mm
Type of product	Lathe chuck accessories