



Flange blank for geared scroll chuck, External Ø D: 210 mm



Order data

Order number	317000 210
GTIN	4019208002989
Item class	33R

Description

Version:

Cleanly cast, unmachined, shot blasted, large allowance.

Application:

Attachment of **chucks with recessed mount to DIN 6350 to spindle noses DIN 800**. The adaptor plate blank must be machined and fitted to the machine and chuck.

Material:

Cast iron

Suitable for :

Three-jaw lathe chuck No. 310100; 310500, four-jaw lathe chuck **No. 312000; 312500** and combi lathe chuck **No. 315630**.

suitable for chuck Ø: 200 mm

Collar Ø d₂: 92 mm

Bore Ø d₃: 40 mm

Height h₁: 66 mm

Flange thickness h₂: 22 mm

Technical description

suitable for chuck Ø	200 mm
----------------------	--------

External \varnothing D	210 mm
Bore \varnothing d ₃	40 mm
Collar \varnothing d ₂	92 mm
Height h ₁	66 mm
Flange thickness h ₂	22 mm
Type of product	Lathe chuck accessories