



Bar holder, Shank Ø d1: 25mm



Order data

Order number	319705 25
GTIN	4045197673251
Item class	32B

Description

Version:

- Anodised housing of high-tensile aluminium with diamond dust-coated roller bodies.
- Steplessly adjustable from 1 – 70 mm.
- Suitable for round, hexagonal and square material.
- Integral adjustment aid with scales.
- General-purpose cylindrical bar holder.

Advantage:

For quick adjustment to the material diameter.

Application:

Suitable for disc turrets and radial turrets.

Supplied with:

Bar gripper with roller bodies, interchangeable jaws and L-wrench for hexagon socket screws for changing the roller bodies and interchangeable jaws.

Note:

Suitable VDI adaptor in the spare parts list, see No. 319707 size 20 / 30.

Technical description

Shank Ø D ₁	25 mm
Length	55 mm
Width	75 mm
Height	42 mm
Type of product	Bar holder

Accessories

Bar holder adapter Shank Ø d1 20 mm	319707 20
Bar holder adapter Shank Ø d1 30 mm	319707 30