

**Clamping head soft, SK 80, Initial bore Ø: 8mm****Order data**

Order number	329946 8
GTIN	2050001924186
Item class	33H

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

**Application:**

Versatile application range: machining centres, measuring machines, and pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Initial bore Ø	8 mm
Hardness	60 HR
Profile	round
Length L	53 mm
Adapter	SK 80

Type of product

Clamping head