

**Bench grinder DS with dust extraction, 400 V, Type: DS04/175A****Order data**

Order number	077514 DS04/175A
GTIN	2050001674104
Item class	03S

**Description****Version:**

Double-ended bench grinding machine with extraction system incorporated in the base. Grinding dust is effectively collected by a water filter and downstream plastic coarse filter and fine filter. **Supplied without grinding wheels.**

**Note:**

Suitable grinding wheels can be found from No. 596100.

Power consumption: 250 W

maximum speed: 2900 min<sup>-1</sup>

Abrasive disc Ø D: 175 mm

Abrasive disc width T: 25 mm

Abrasive disc hole Ø H: 51 mm

Extraction conveying volume: 6 m<sup>3</sup>/min

**Technical description**

Power consumption	250 W
Weight	83 kg

maximum speed	2900 min <sup>-1</sup>
Manufacturer's designation	DS04/175A
Extraction conveying volume	6 m <sup>3</sup> /min
Abrasive disc width T	25 mm
Abrasive disc hole Ø H	51 mm
Abrasive disc Ø D	175 mm
Power supply	Mains operated
Type of product	Double grinding machine

---

## Accessories

Bench grinding wheel D×T×H (mm) Type EK60	596350 EK60
Bench grinding wheel D×T×H (mm) Type NK36	596350 NK36
Bench grinding wheel D×T×H (mm) Type NK60	596350 NK60
Bench grinding wheel D×T×H (mm) Type C800	596350 C800
Bench grinding wheel D×T×H (mm) Type EK80	596350 EK80
Bench grinding wheel D×T×H (mm) Type SC80	596350 SC80