



**Clamping head smooth, Top 65, Clamping Ø (0.5 mm increments): 40,5mm**



## Order data

Order number	329970 40,5
GTIN	2050001926265
Item class	33H

## Description

### Version:

Clamping heads, **round profile**, in 0.5 mm increments. Please specify required clamping Ø with order.

Smooth version for precision machining.

### Advantage:

- **25% greater clamping force than clamping head RD.**
- **No radial movement between clamping head and clamping element mounting, therefore immune to dirt.**
- **Unique stiffness due to large seating area of the clamping segments.**

### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

### Recommendation:

**Clamping heads for special profiles to your individual requirements on request.**

### Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

## Technical description

Clamping Ø	40.5 mm
------------	---------

Profile	round
Clamping face	smooth
Hardness	60 HR
Length L	49 mm
Adapter	Top 65
Type of product	Clamping head