

EWS
ER collet chuck VARIA, V3, for ER collet size: 20

Order data

Order number	319801 20
GTIN	4045197317537
Item class	33E

Description
Advantage:

- **Quick change using a single clamping point, therefore tool change without risk of injury.**
- **Cutter tools lie pre-set at the machine.**
- **Compact design - low unit costs.**

Application:

Mainly for drilling and centring.

Note:

Maximum tightening torque for VX3 and VX4 is 5.7 Nm, which can be achieved using the appropriate torque screwdriver No. 211750 size 5.7. Maximum tightening torque for V3, V4 and V5 is 10 Nm. When releasing the deposits, do not travel beyond the stop.

Overhang dimension A: 27 mm

External Ø D: 34 mm

Technical description

for ER collets	20
Overhang dimension A	27 mm
External Ø D	34 mm
Adapter	V3

Type of product

Collet chuck