



Indexable drill toolholder VARIA, V3, Clamping range \varnothing D1: 8mm



Order data

Order number

319821 8

GTIN

Item class

33E

Description

Advantage:

- **Quick change using a single clamping point, therefore tool change without risk of injury.**
- **Cutter tools lie pre-set at the machine.**
- **Compact design - low unit costs.**

Application:

For clamping tools with drive flats.

Note:

Maximum tightening torque for VX3 and VX4 is 5.7 Nm, which can be achieved using the appropriate torque screwdriver No. 211750 size 5.7. Maximum tightening torque for V3, V4 and V5 is 10 Nm. When releasing the deposits, do not travel beyond the stop.

Extra short version available on request.

Technical description

Clamping \varnothing D₁

8 mm

Overhang dimension A

17 mm

External \varnothing D

25 mm

Adapter

V3

Type of product

Side lock arbor