



Clamping head soft, SK 80, Initial bore \varnothing : 60mm



Order data

Order number	329946 60
GTIN	2050001924216
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Initial bore \varnothing	60 mm
Hardness	60 HR
Profile	round
Length L	53 mm
Adapter	SK 80

Type of product

Clamping head