



Reducing adapter, Shank \varnothing d1 / clamping \varnothing d2: 50/40mm



Order data

Order number	319426 50/40
GTIN	4045197586926
Item class	32V

Description

Version:

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Suitable for internal cooling, not slotted. Tool is fixed and clamped with 2 clamping screws.

Application:

For \varnothing reduction for tools with plain shanks.

Technical description

Version	Slot
l_1	75 mm
l_2	5 mm
$\varnothing d_4$	54 mm
Shank $\varnothing D_1$	50 mm
Clamping range $\varnothing d_2$	40 mm
Type of product	Reducing adapter

