

**Stationary chuck MANOK plus, Type / size: RD65****Order data**

Order number	329960 RD65
GTIN	2050001925992
Item class	33H

Description**Version:**

Stationary chuck of solid cast. High clamping force, precision, and stiffness. Ground face for horizontal mounting, integral stop.

Application:

Versatile application e. g. machining centres, measuring machines, pillar drills etc.

Suitable for:

Clamping heads No. 329910 – 329946.

Supplied with:

Including 1 chuck key.

Note:

Use changing device No. 329832 size 65.

Technical description

Length L	184 mm
Width B	184 mm
Height H	120 mm
Weight	23.5 kg

Arbor size	RD65
Pitch circle Ø	126 mm
Repetition accuracy	0.01 mm
Spacing of attachment holes	126 mm
maximum clamping force	105 kN
Clamping range	4 - 65 mm
Depth stop	92 mm
Slot size tolerance	20 H7
Type of product	Vice

Accessories

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 21,5 mm	329934 21,5
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 9 mm	329932 9
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 52 mm	329934 52
Clamping headsmooth Clamping Ø (0.5 mm increments) 56 mm	329930 56
Clamping headsmooth Clamping Ø (0.5 mm increments) 26,5 mm	329930 26,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 55,5 mm	329934 55,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 31 mm	329930 31
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 29,5 mm	329934 29,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 22 mm	329934 22
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 31,5 mm	329934 31,5

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 56,5 mm	329934 56,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 20,5 mm	329934 20,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 26,5 mm	329934 26,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 59,5 mm	329930 59,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 53 mm	329930 53
Clamping headsmooth Clamping Ø (0.5 mm increments) 24 mm	329930 24
Clamping headsmooth Clamping Ø (0.5 mm increments) 39,5 mm	329930 39,5
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 8,5 mm	329932 8,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 10,5 mm	329930 10,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 11 mm	329934 11
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 33,5 mm	329934 33,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 34 mm	329930 34
Clamping headsmooth Clamping Ø (0.5 mm increments) 46,5 mm	329930 46,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 55 mm	329930 55
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 62 mm	329934 62
Clamping headsmooth Clamping Ø (0.5 mm increments) 4 mm	329930 4
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 43 mm	329934 43
	329930 21

Clamping headsmooth Clamping Ø (0.5 mm increments) 21 mm	
Clamping headsmooth Clamping Ø (0.5 mm increments) 16 mm	329930 16
Clamping headsmooth Clamping Ø (0.5 mm increments) 11 mm	329930 11
Clamping headsmooth Clamping Ø (0.5 mm increments) 52 mm	329930 52
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 42,5 mm	329934 42,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 46 mm	329934 46
Clamping headsmooth Clamping Ø (0.5 mm increments) 31,5 mm	329930 31,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 5 mm	329930 5
Clamping headsmooth Clamping Ø (0.5 mm increments) 12,5 mm	329930 12,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 22 mm	329930 22
Clamping headsmooth Clamping Ø (0.5 mm increments) 37 mm	329930 37
Clamping headsmooth Clamping Ø (0.5 mm increments) 55,5 mm	329930 55,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 19 mm	329934 19
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 63,5 mm	329934 63,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 60,5 mm	329934 60,5
Clamping headsoft Initial bore Ø 40 mm	329936 40
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 44,5 mm	329934 44,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 27 mm	329930 27

Clamping headsmooth Clamping Ø (0.5 mm increments) 51,5 mm	329930 51,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 23 mm	329934 23
Clamping headsmooth Clamping Ø (0.5 mm increments) 39 mm	329930 39
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 31 mm	329934 31
Clamping headsmooth Clamping Ø (0.5 mm increments) 13,5 mm	329930 13,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 54 mm	329930 54
Clamping headsmooth Clamping Ø (0.5 mm increments) 60 mm	329930 60
Clamping headsmooth Clamping Ø (0.5 mm increments) 49,5 mm	329930 49,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 11,5 mm	329930 11,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 33 mm	329934 33
Clamping headsmooth Clamping Ø (0.5 mm increments) 18 mm	329930 18
Clamping headsmooth Clamping Ø (0.5 mm increments) 62,5 mm	329930 62,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 46 mm	329930 46
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 39,5 mm	329934 39,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 57,5 mm	329934 57,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 23 mm	329930 23
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 30 mm	329934 30
	329934 18

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 18 mm

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 34 mm

329934 34

Clamping headsmooth Clamping Ø (0.5 mm increments)
38,5 mm

329930 38,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
32,5 mm

329930 32,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
23,5 mm

329930 23,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
42 mm

329930 42

Clamping headsmooth Clamping Ø (0.5 mm increments)
13 mm

329930 13

Clamping headsmooth Clamping Ø (0.5 mm increments)
36,5 mm

329930 36,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 32 mm

329934 32

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 36,5 mm

329934 36,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
53,5 mm

329930 53,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
40 mm

329930 40

Clamping headsmooth Clamping Ø (0.5 mm increments)
16,5 mm

329930 16,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 57 mm

329934 57

Clamping headsmooth Clamping Ø (0.5 mm increments)
64 mm

329930 64

Clamping headsmooth Clamping Ø (0.5 mm increments)
35,5 mm

329930 35,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
29,5 mm

329930 29,5

329934 53

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 53 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 54,5 mm	329934 54,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 25,5 mm	329930 25,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 58,5 mm	329930 58,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 58,5 mm	329934 58,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 53,5 mm	329934 53,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 15,5 mm	329934 15,5
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 10 mm	329932 10
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 38 mm	329934 38
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 61 mm	329934 61
Clamping headsmooth Clamping Ø (0.5 mm increments) 29 mm	329930 29
Clamping headsmooth Clamping Ø (0.5 mm increments) 61,5 mm	329930 61,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 60 mm	329934 60
Clamping headsmooth Clamping Ø (0.5 mm increments) 21,5 mm	329930 21,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 34,5 mm	329930 34,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 48 mm	329934 48
Clamping headsmooth Clamping Ø (0.5 mm increments) 52,5 mm	329930 52,5
	329934 65

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 65 mm	
Clamping headsmooth Clamping Ø (0.5 mm increments) 48,5 mm	329930 48,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 61,5 mm	329934 61,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 54 mm	329934 54
Clamping headsmooth Clamping Ø (0.5 mm increments) 62 mm	329930 62
Clamping headsmooth Clamping Ø (0.5 mm increments) 28 mm	329930 28
Clamping headsmooth Clamping Ø (0.5 mm increments) 56,5 mm	329930 56,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 45,5 mm	329934 45,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 25 mm	329934 25
Clamping headsmooth Clamping Ø (0.5 mm increments) 51 mm	329930 51
Clamping headsmooth Clamping Ø (0.5 mm increments) 44 mm	329930 44
Clamping headsmooth Clamping Ø (0.5 mm increments) 38 mm	329930 38
Clamping headsmooth Clamping Ø (0.5 mm increments) 42,5 mm	329930 42,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 57,5 mm	329930 57,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 7,5 mm	329930 7,5
Clamping headsoft Initial bore Ø 20 mm	329936 20
Clamping headsmooth Clamping Ø (0.5 mm increments) 33 mm	329930 33
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 43,5 mm	329934 43,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 9 mm	329930 9
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 28 mm	329934 28
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 59,5 mm	329934 59,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 24,5 mm	329930 24,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 21 mm	329934 21
Clamping headsmooth Clamping Ø (0.5 mm increments) 49 mm	329930 49
Clamping headsmooth Clamping Ø (0.5 mm increments) 58 mm	329930 58
Clamping headsmooth Clamping Ø (0.5 mm increments) 8,5 mm	329930 8,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 37 mm	329934 37
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 51 mm	329934 51
Clamping headsmooth Clamping Ø (0.5 mm increments) 12 mm	329930 12
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 12 mm	329934 12
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 13 mm	329934 13
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 32,5 mm	329934 32,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 63,5 mm	329930 63,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 27 mm	329934 27
Clamping headsmooth Clamping Ø (0.5 mm increments) 4,5 mm	329930 4,5
	329934 35

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 35 mm

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 34,5 mm

329934 34,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 30,5 mm

329934 30,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
19,5 mm

329930 19,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
6,5 mm

329930 6,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 17 mm

329934 17

Clamping headsmooth Clamping Ø (0.5 mm increments)
48 mm

329930 48

Clamping headsmooth Clamping Ø (0.5 mm increments)
43 mm

329930 43

Clamping headsmooth Clamping Ø (0.5 mm increments)
47 mm

329930 47

Clamping headsmooth Clamping Ø (0.5 mm increments) 7
mm

329930 7

Clamping headsmooth Clamping Ø (0.5 mm increments)
47,5 mm

329930 47,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 44 mm

329934 44

Clamping headwith transverse serrations. Clamping Ø (0.5
mm increments) 8 mm

329932 8

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 59 mm

329934 59

Clamping headsmooth Clamping Ø (0.5 mm increments)
57 mm

329930 57

Clamping headsmooth Clamping Ø (0.5 mm increments)
54,5 mm

329930 54,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
5,5 mm

329930 5,5

329934 14

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 14 mm

Clamping headsmooth Clamping Ø (0.5 mm increments)
9,5 mm

329930 9,5

Clamping headsoft Initial bore Ø 5 mm

329936 5

Clamping headsmooth Clamping Ø (0.5 mm increments)
10 mm

329930 10

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 11,5 mm

329934 11,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 48,5 mm

329934 48,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
50,5 mm

329930 50,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 50,5 mm

329934 50,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
15 mm

329930 15

Clamping headsmooth Clamping Ø (0.5 mm increments)
32 mm

329930 32

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 19,5 mm

329934 19,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 56 mm

329934 56

Clamping headsmooth Clamping Ø (0.5 mm increments)
17,5 mm

329930 17,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
28,5 mm

329930 28,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 64,5 mm

329934 64,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 47,5 mm

329934 47,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
45 mm

329930 45

Clamping headsmooth Clamping Ø (0.5 mm increments)
18,5 mm

329930 18,5

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 42 mm	329934 42
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 24,5 mm	329934 24,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 41 mm	329934 41
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 52,5 mm	329934 52,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 20 mm	329934 20
Clamping headsmooth Clamping Ø (0.5 mm increments) 40,5 mm	329930 40,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 30,5 mm	329930 30,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 41,5 mm	329930 41,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 51,5 mm	329934 51,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 33,5 mm	329930 33,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 37,5 mm	329930 37,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 27,5 mm	329934 27,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 14,5 mm	329930 14,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 36 mm	329934 36
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 35,5 mm	329934 35,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 46,5 mm	329934 46,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 47 mm	329934 47
	329930 61

Clamping headsmooth Clamping Ø (0.5 mm increments) 61 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 29 mm	329934 29
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 23,5 mm	329934 23,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 35 mm	329930 35
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 16 mm	329934 16
Clamping headsmooth Clamping Ø (0.5 mm increments) 65 mm	329930 65
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 25,5 mm	329934 25,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 63 mm	329934 63
Clamping headsmooth Clamping Ø (0.5 mm increments) 44,5 mm	329930 44,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 24 mm	329934 24
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 37,5 mm	329934 37,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 16,5 mm	329934 16,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 49 mm	329934 49
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 14,5 mm	329934 14,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 12,5 mm	329934 12,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 38,5 mm	329934 38,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 20,5 mm	329930 20,5
	329930 60,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 60,5 mm	
Clamping headsmooth Clamping Ø (0.5 mm increments) 59 mm	329930 59
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 15 mm	329934 15
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 18,5 mm	329934 18,5
Clamping headsoft Initial bore Ø 8 mm	329936 8
Clamping headsmooth Clamping Ø (0.5 mm increments) 6 mm	329930 6
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 49,5 mm	329934 49,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 36 mm	329930 36
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 26 mm	329934 26
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 17,5 mm	329934 17,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 45,5 mm	329930 45,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 28,5 mm	329934 28,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 39 mm	329934 39
Clamping headsmooth Clamping Ø (0.5 mm increments) 43,5 mm	329930 43,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 22,5 mm	329930 22,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 27,5 mm	329930 27,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 14 mm	329930 14
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 55 mm	329934 55

Clamping headsmooth Clamping Ø (0.5 mm increments) 25 mm	329930 25
Clamping headsmooth Clamping Ø (0.5 mm increments) 26 mm	329930 26
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 58 mm	329934 58
Clamping headsmooth Clamping Ø (0.5 mm increments) 50 mm	329930 50
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 41,5 mm	329934 41,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 40 mm	329934 40
Clamping headsmooth Clamping Ø (0.5 mm increments) 41 mm	329930 41
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 13,5 mm	329934 13,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 64,5 mm	329930 64,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 15,5 mm	329930 15,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 8 mm	329930 8
Clamping headsmooth Clamping Ø (0.5 mm increments) 30 mm	329930 30
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 22,5 mm	329934 22,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 19 mm	329930 19
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 45 mm	329934 45
Clamping headsmooth Clamping Ø (0.5 mm increments) 63 mm	329930 63
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 40,5 mm	329934 40,5
	329930 20

Clamping headsmooth Clamping \varnothing (0.5 mm increments)
20 mm

Clamping headwith transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 50 mm

329934 50

Clamping headwith transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 64 mm

329934 64

Clamping headsmooth Clamping \varnothing (0.5 mm increments)
17 mm

329930 17

Clamping headwith transverse serrations. Clamping \varnothing (0.5
mm increments) 9,5 mm

329932 9,5

Clamping headwith transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 62,5 mm

329934 62,5