

**Stationary chuck MANOK plus, Type / size: SE65****Order data**

Order number	329960 SE65
GTIN	2050001926005
Item class	33H

Description**Version:**

Stationary chuck of solid cast. High clamping force, precision, and stiffness. Ground face for horizontal mounting, integral stop. Clamping heads for special profiles to your individual requirements on request.

Application:

Versatile application e. g. machining centres, measuring machines, pillar drills etc.

Suitable for:

Clamping heads No. 329970 – 329976.

Supplied with:

Including 1 chuck key.

Note:

Use changing device No. 329832 size 65.

Technical description

Weight	23.5 kg
Height H	120 mm
Width B	184 mm

Length L	184 mm
Arbor size	SE65
Pitch circle Ø	126 mm
Repetition accuracy	0.01 mm
maximum clamping force	45 kN
Spacing of attachment holes	126 mm
Clamping range	4 - 65 mm
Slot size tolerance	20 H7
Depth stop	92 mm
Type of product	Vice

Accessories

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 34 mm	329974 34
Clamping headsmooth Clamping Ø (0.5 mm increments) 19 mm	329970 19
Clamping headsmooth Clamping Ø (0.5 mm increments) 29 mm	329970 29
Clamping headsmooth Clamping Ø (0.5 mm increments) 33,5 mm	329970 33,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 47 mm	329970 47
Clamping headsmooth Clamping Ø (0.5 mm increments) 49 mm	329970 49
Clamping headsoft Initial bore Ø 5 mm	329976 5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 17,5 mm	329974 17,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 48 mm	329974 48
Clamping headsmooth Clamping Ø (0.5 mm increments) 10,5 mm	329970 10,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 37,5 mm	329970 37,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 20,5 mm	329974 20,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 20,5 mm	329970 20,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 44 mm	329970 44
Clamping headsmooth Clamping Ø (0.5 mm increments) 43,5 mm	329970 43,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 51,5 mm	329974 51,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 54 mm	329970 54
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 18,5 mm	329974 18,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 62,5 mm	329974 62,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 12,5 mm	329970 12,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 60,5 mm	329974 60,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 51 mm	329970 51
Clamping headsmooth Clamping Ø (0.5 mm increments) 48,5 mm	329970 48,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 6,5 mm	329970 6,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 21 mm	329974 21
Clamping headsmooth Clamping Ø (0.5 mm increments) 65 mm	329970 65
Clamping headsoft Initial bore Ø 20 mm	329976 20
Clamping headsmooth Clamping Ø (0.5 mm increments) 27 mm	329970 27

Clamping headsmooth Clamping Ø (0.5 mm increments) 23 mm	329970 23
Clamping headsmooth Clamping Ø (0.5 mm increments) 63,5 mm	329970 63,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 12,5 mm	329974 12,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 63 mm	329974 63
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 27 mm	329974 27
Clamping headsmooth Clamping Ø (0.5 mm increments) 49,5 mm	329970 49,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 51,5 mm	329970 51,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 55 mm	329974 55
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 44 mm	329974 44
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 33 mm	329974 33
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 8,5 mm	329972 8,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 44,5 mm	329970 44,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 12 mm	329974 12
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 30 mm	329974 30
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 30,5 mm	329974 30,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 64 mm	329974 64
Clamping headsmooth Clamping Ø (0.5 mm increments) 5 mm	329970 5
	329970 29,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 29,5 mm	
Clamping headsmooth Clamping Ø (0.5 mm increments) 50,5 mm	329970 50,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 17 mm	329970 17
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 37 mm	329974 37
Clamping headsmooth Clamping Ø (0.5 mm increments) 47,5 mm	329970 47,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 56,5 mm	329974 56,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 13,5 mm	329974 13,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 51 mm	329974 51
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 36 mm	329974 36
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 39,5 mm	329974 39,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 9 mm	329970 9
Clamping headsmooth Clamping Ø (0.5 mm increments) 21 mm	329970 21
Clamping headsmooth Clamping Ø (0.5 mm increments) 39 mm	329970 39
Clamping headsmooth Clamping Ø (0.5 mm increments) 54,5 mm	329970 54,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 31 mm	329970 31
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 53,5 mm	329974 53,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 50 mm	329970 50
	329970 45,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 45,5 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 14,5 mm	329974 14,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 18 mm	329970 18
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 13 mm	329974 13
Clamping headsmooth Clamping Ø (0.5 mm increments) 16 mm	329970 16
Clamping headsmooth Clamping Ø (0.5 mm increments) 53 mm	329970 53
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 19 mm	329974 19
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 57 mm	329974 57
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 47,5 mm	329974 47,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 29 mm	329974 29
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 44,5 mm	329974 44,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 57,5 mm	329974 57,5
Clamping headsoft Initial bore Ø 40 mm	329976 40
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 23 mm	329974 23
Clamping headsmooth Clamping Ø (0.5 mm increments) 62,5 mm	329970 62,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 22 mm	329974 22
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 27,5 mm	329974 27,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 35,5 mm	329974 35,5

Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 54 mm	329974 54
Clamping headsmooth Clamping Ø (0.5 mm increments) 33 mm	329970 33
Clamping headsmooth Clamping Ø (0.5 mm increments) 41 mm	329970 41
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 61,5 mm	329974 61,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 38 mm	329974 38
Clamping headsmooth Clamping Ø (0.5 mm increments) 15 mm	329970 15
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 48,5 mm	329974 48,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 17 mm	329974 17
Clamping headsmooth Clamping Ø (0.5 mm increments) 28,5 mm	329970 28,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 27,5 mm	329970 27,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 57 mm	329970 57
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 24 mm	329974 24
Clamping headsmooth Clamping Ø (0.5 mm increments) 7,5 mm	329970 7,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 25 mm	329974 25
Clamping headsmooth Clamping Ø (0.5 mm increments) 43 mm	329970 43
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 63,5 mm	329974 63,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 59,5 mm	329974 59,5
	329970 26,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 26,5 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 38,5 mm	329974 38,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 11,5 mm	329970 11,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 42,5 mm	329974 42,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 28 mm	329974 28
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 28,5 mm	329974 28,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 13 mm	329970 13
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 9,5 mm	329972 9,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 4,5 mm	329970 4,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 52 mm	329970 52
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 32,5 mm	329974 32,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 52,5 mm	329974 52,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 64 mm	329970 64
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 56 mm	329974 56
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 61 mm	329974 61
Clamping headsmooth Clamping Ø (0.5 mm increments) 40 mm	329970 40
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 22,5 mm	329974 22,5
	329970 35

Clamping headsmooth Clamping Ø (0.5 mm increments) 35 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 40 mm	329974 40
Clamping headsmooth Clamping Ø (0.5 mm increments) 14 mm	329970 14
Clamping headsmooth Clamping Ø (0.5 mm increments) 4 mm	329970 4
Clamping headsmooth Clamping Ø (0.5 mm increments) 60 mm	329970 60
Clamping headsmooth Clamping Ø (0.5 mm increments) 38 mm	329970 38
Clamping headsmooth Clamping Ø (0.5 mm increments) 31,5 mm	329970 31,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 34 mm	329970 34
Clamping headsmooth Clamping Ø (0.5 mm increments) 11 mm	329970 11
Clamping headsmooth Clamping Ø (0.5 mm increments) 39,5 mm	329970 39,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 29,5 mm	329974 29,5
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 8 mm	329972 8
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 24,5 mm	329974 24,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 11,5 mm	329974 11,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 46,5 mm	329970 46,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 20 mm	329970 20
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 58 mm	329974 58
	329974 32

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 32 mm

Clamping headsmooth Clamping Ø (0.5 mm increments)
45 mm

329970 45

Clamping headsmooth Clamping Ø (0.5 mm increments) 7
mm

329970 7

Clamping headsmooth Clamping Ø (0.5 mm increments)
16,5 mm

329970 16,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
8,5 mm

329970 8,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
32 mm

329970 32

Clamping headsmooth Clamping Ø (0.5 mm increments)
61 mm

329970 61

Clamping headsmooth Clamping Ø (0.5 mm increments)
10 mm

329970 10

Clamping headsmooth Clamping Ø (0.5 mm increments)
55 mm

329970 55

Clamping headsmooth Clamping Ø (0.5 mm increments)
14,5 mm

329970 14,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
46 mm

329970 46

Clamping headsmooth Clamping Ø (0.5 mm increments) 6
mm

329970 6

Clamping headsmooth Clamping Ø (0.5 mm increments)
17,5 mm

329970 17,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
9,5 mm

329970 9,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
58,5 mm

329970 58,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 45 mm

329974 45

Clamping headsmooth Clamping Ø (0.5 mm increments)
30,5 mm

329970 30,5

329974 50

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 50 mm

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 46,5 mm

329974 46,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 19,5 mm

329974 19,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
59,5 mm

329970 59,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
5,5 mm

329970 5,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 49 mm

329974 49

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 31,5 mm

329974 31,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 20 mm

329974 20

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 41,5 mm

329974 41,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 41 mm

329974 41

Clamping headsmooth Clamping Ø (0.5 mm increments)
22 mm

329970 22

Clamping headsmooth Clamping Ø (0.5 mm increments)
57,5 mm

329970 57,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
19,5 mm

329970 19,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
42 mm

329970 42

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 15 mm

329974 15

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 49,5 mm

329974 49,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
62 mm

329970 62

329974 26,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 26,5 mm

Clamping head smooth Clamping \varnothing (0.5 mm increments)
60,5 mm

329970 60,5

Clamping head with transverse serrations. Clamping \varnothing (0.5
mm increments) 9 mm

329972 9

Clamping head smooth Clamping \varnothing (0.5 mm increments)
34,5 mm

329970 34,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 46 mm

329974 46

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 58,5 mm

329974 58,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 43 mm

329974 43

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 59 mm

329974 59

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 64,5 mm

329974 64,5

Clamping head smooth Clamping \varnothing (0.5 mm increments)
58 mm

329970 58

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 16 mm

329974 16

Clamping head smooth Clamping \varnothing (0.5 mm increments)
25,5 mm

329970 25,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 42 mm

329974 42

Clamping head smooth Clamping \varnothing (0.5 mm increments)
40,5 mm

329970 40,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 11 mm

329974 11

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 45,5 mm

329974 45,5

Clamping head with transverse and longitudinal serrations
Clamping \varnothing (0.5 mm increments) 52 mm

329974 52

329970 26

Clamping headsmooth Clamping Ø (0.5 mm increments) 26 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 36,5 mm	329974 36,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 22,5 mm	329970 22,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 39 mm	329974 39
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 43,5 mm	329974 43,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 26 mm	329974 26
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 21,5 mm	329974 21,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 30 mm	329970 30
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 16,5 mm	329974 16,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 53,5 mm	329970 53,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 15,5 mm	329974 15,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 40,5 mm	329974 40,5
Clamping headsoft Initial bore Ø 8 mm	329976 8
Clamping headwith transverse serrations. Clamping Ø (0.5 mm increments) 10 mm	329972 10
Clamping headsmooth Clamping Ø (0.5 mm increments) 25 mm	329970 25
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 25,5 mm	329974 25,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 18,5 mm	329970 18,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 37,5 mm	329974 37,5

Clamping headsmooth Clamping Ø (0.5 mm increments) 55,5 mm	329970 55,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 63 mm	329970 63
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 54,5 mm	329974 54,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 42,5 mm	329970 42,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 23,5 mm	329970 23,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 38,5 mm	329970 38,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 36 mm	329970 36
Clamping headsmooth Clamping Ø (0.5 mm increments) 8 mm	329970 8
Clamping headsmooth Clamping Ø (0.5 mm increments) 61,5 mm	329970 61,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 33,5 mm	329974 33,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 35 mm	329974 35
Clamping headsmooth Clamping Ø (0.5 mm increments) 12 mm	329970 12
Clamping headsmooth Clamping Ø (0.5 mm increments) 56,5 mm	329970 56,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 24 mm	329970 24
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 23,5 mm	329974 23,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 55,5 mm	329974 55,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 65 mm	329974 65
	329970 28

Clamping headsmooth Clamping Ø (0.5 mm increments) 28 mm	
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 31 mm	329974 31
Clamping headsmooth Clamping Ø (0.5 mm increments) 48 mm	329970 48
Clamping headsmooth Clamping Ø (0.5 mm increments) 52,5 mm	329970 52,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 35,5 mm	329970 35,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 47 mm	329974 47
Clamping headsmooth Clamping Ø (0.5 mm increments) 24,5 mm	329970 24,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 21,5 mm	329970 21,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 37 mm	329970 37
Clamping headsmooth Clamping Ø (0.5 mm increments) 36,5 mm	329970 36,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 64,5 mm	329970 64,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 34,5 mm	329974 34,5
Clamping headsmooth Clamping Ø (0.5 mm increments) 13,5 mm	329970 13,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 62 mm	329974 62
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 53 mm	329974 53
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 50,5 mm	329974 50,5
Clamping headwith transverse and longitudinal serrations Clamping Ø (0.5 mm increments) 60 mm	329974 60
	329970 15,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
15,5 mm

Clamping headsmooth Clamping Ø (0.5 mm increments)
32,5 mm

329970 32,5

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 18 mm

329974 18

Clamping headwith transverse and longitudinal serrations
Clamping Ø (0.5 mm increments) 14 mm

329974 14

Clamping headsmooth Clamping Ø (0.5 mm increments)
56 mm

329970 56

Clamping headsmooth Clamping Ø (0.5 mm increments)
41,5 mm

329970 41,5

Clamping headsmooth Clamping Ø (0.5 mm increments)
59 mm

329970 59