



## Clamping head with transverse and longitudinal serrations., SK 80, Clamping Ø (1 mm increments): 67mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329944 67     |
| GTIN         | 2050001924049 |
| Item class   | 33H           |

### Description

#### Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

With transverse and longitudinal serrations for raw material.

#### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|               |  |
|---------------|--|
| Clamping Ø    | 67 mm                                  |
| Hardness      | 60 HR                                  |
| Clamping face | Transverse and longitudinal serrations |
| Profile       | round                                  |

|                 |               |
|-----------------|---------------|
| Length L        | 53 mm         |
| Adapter         | SK 80         |
| Type of product | Clamping head |