

**EWS**
**ER collet chuck VARIA, V4, for ER collet size: 16**

**Order data**

Order number	319803 16
GTIN	4045197317568
Item class	33E

**Description**
**Advantage:**

- **Quick change using a single clamping point, therefore tool change without risk of injury.**
- **Cutter tools lie pre-set at the machine.**
- **Compact design - low unit costs.**

**Application:**

Mainly for drilling and centring.

**Note:**

Maximum tightening torque for VX3 and VX4 is 5.7 Nm, which can be achieved using the appropriate torque screwdriver No. 211750 size 5.7. Maximum tightening torque for V3, V4 and V5 is 10 Nm. When releasing the deposits, do not travel beyond the stop.

Overhang dimension A: 50 mm

External Ø D: 28 mm

**Technical description**

Overhang dimension A	50 mm
for ER collets	16
External Ø D	28 mm
Adapter	V4

Type of product

Collet chuck