

**Compact angle grinder, Type: 722177****Order data**

Order number	077111 722177
GTIN	4014586875316
Item class	03F

Description**Version:****FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: WSG 11-125

Power consumption: 1100 W

maximum speed: 11,000 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 33 mm

Weight: 2.2 kg

Technical description

Weight	2.2 kg
--------	--------

Restart block	yes
Manufacturer's designation	WSG 11-125
maximum vibration to EN	6 m/s ²
Dead man's circuit	no
maximum cutting depth	33 mm
Power consumption	1100 W
maximum speed	11,000 min ⁻¹
maximum disc Ø	125 mm
Special features	short body
Power supply	Mains operated
Type of product	Angle grinder