

**Garant**
**Shrink-fit chuck, HSK-A 63 A = 120, Clamping range  $\varnothing$  D1: 3mm**

**Order data**

Order number	308189 3
GTIN	4045197290946
Item class	31A

**Description**
**Version:**

From clamping  $\varnothing$  D<sub>1</sub> 6 mm with tapped holes for balancing screws.  
Integral length adjustment of the tool from clamping  $\varnothing$  D<sub>1</sub> 6 mm (adjustment travel 10 mm).

- **High-temperature steel.**
- **Sizes 3 – 5 for carbide, from size 6 for HSS and carbide.**
- **With RFID/Balluffchip bore.**

**GARANT:** HSK mating faces machined. **All shanks hard turned (for smooth running!).**

**Application:**

- **For holding end mills and drills with parallel shank to h6 tolerance.**
- **Suitable for inductive, contact and hot air shrink-fit units.**

**Supplied with:**

For chucks with length adjustment including a length adjustment screw (from clamping  $\varnothing$  D<sub>1</sub> 6 mm).

**Optional extras:**

Coolant tube No. 309880, socket wrench No. 309890, shrink-fit chuck extension No. 302410 – 302416, shrink-fit units No. 354210 – 354450, balancing screw set No. 309906 180.

**Technical description**

$\varnothing$ D <sub>2</sub>	12 mm
Overhang dimension A	120 mm
Clamping $\varnothing$ D <sub>1</sub>	3 mm

External Ø D	17 mm
Adapter	HSK-A 63 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Subframe cupboard	354290
Cooling adapter short4.5° for clamping Ø 3-5,9 mm	354235 3-5,9
Cooling unit Type CU1	354215 CU1
Screening plate for coilSU1 for clamping Ø 3-5 mm	354240 3-5
Cooling adapter long4.5° for clamping Ø 3-5,9 mm	354236 3-5,9
Shrink-fit unit Type SU1	354210 SU1