



Clamping head smooth, Top 65, Clamping Ø (0.5 mm increments): 9,5mm



Order data

Order number	329970 9,5
GTIN	2050001926760
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm increments. Please specify required clamping Ø with order.**

Smooth version for precision machining.

Advantage:

- **25% greater clamping force than clamping head RD.**
- **No radial movement between clamping head and clamping element mounting, therefore immune to dirt.**
- **Unique stiffness due to large seating area of the clamping segments.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Recommendation:

Clamping heads for special profiles to your individual requirements on request.

Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping Ø	9.5 mm
------------	--------

Hardness	60 HR
Clamping face	smooth
Profile	round
Length L	49 mm
Adapter	Top 65
Type of product	Clamping head