



Single-speed power drill, Type: HDE13RQX



Order data

Order number	075210 HDE13RQX
GTIN	4002395241576
Item class	03M

Description

Version:

Milwaukee hand-held power drill –

- 13 mm power drill with 94 Nm torque.
- Electronic speed control.
- FIXTEC spindle lock for quick drill change.
- Robust, fully insulated metal gearbox.
- QUIK-LOK cable quick-change system.

Advantage:

QUIK-LOK cable.

Supplied with:

Supplied with 1.5 - 13 mm metal quick-change chuck, additional handle, QUIK-LOK cable (4 m), HD box.

Technical description

Weight	2 kg
maximum twist drill size \varnothing in wood	38 mm

Manufacturer's designation	HDE13RQX
Power consumption	950 W
maximum vibration to EN	< 2.5 m/s ²
Reversible	yes
Chuck clamping range	1.5 - 13 mm
maximum twist drill size Ø in steel	13 mm
Drill chuck adapter	1/2 inch – 20 UNF
Speed range	0 - 850 min ⁻¹
Power supply	Mains operated
Suitable for material	Steel
Packaging	Modular case (HD=Heavy Duty)
Type of product	Drill