



Core drilling machine, Type: 727041



Order data

Order number	076520 727041
GTIN	4014586872834
Item class	03F

Description

Version:

- **High magnetic clamping force and safety circuit ensure safe working in any position.**
- **Integral coolant supply for clean cut and long tool life.**
- **Convenient magnetic clamping force display.**
- **Reversible (even for thread tapping).**
- **Weight-optimised design.**

Lightweight core drilling machine, very easy to use, for efficient drilling in the workshop and on site.

2-speed magnetic core drilling machines

- **Feed rate wheel can be switched from one side to the other.**
- **Increased magnetic clamping force.**
- **5-stage speed adjustment and speed setting memory.**

Version of the advertising text:

Lightweight core drilling machine, very easy to use, for efficient drilling in the workshop and on site.

Supplied with:

Supplied with cooling lubricant tank, lashing strap, 1x centring pin, swarf hook, carrying case.

Optional extras:

On request.

Note:

See from No. 119000 for carbide core drills and arbors. Suitable QuickIN-Max arbor and carbide core drills max. DM 100 mm available on request.

Technical description

Speed range 1st speed	130 - 260 min ⁻¹
Length of magnetic base	195 mm
Width	198 mm
Tool arbor shape	QuickIN
maximum twist drill size Ø in steel	16 mm
Width of the magnetic base	90 mm
Weight	13.2 kg
Length	311 mm
maximum countersink Ø	31 mm
Working stroke	145 mm
maximum reamer Ø	16 mm
Manufacturer's designation	KBM50Q
Power consumption	1200 W
AC supply voltage	230 V
Height	730 mm
Speed range 2nd speed	260 - 520 min ⁻¹
maximum core drill Ø in steel	12 - 50 mm
maximum machine tap Ø in steel	M16 mm
Power supply	Mains operated
Packaging	Carrying case
Type of product	Core drilling machine

Accessories

Carbide core drillDepth of cut 35 mm Ø DC 25 mm	119000 25
Carbide core drillDepth of cut 35 mm Ø DC 52 mm	119000 52
Carbide core drillDepth of cut 35 mm Ø DC 15 mm	119000 15
Carbide core drillDepth of cut 35 mm Ø DC 62 mm	119000 62
Carbide core drillDepth of cut 35 mm Ø DC 30 mm	119000 30
Carbide core drillDepth of cut 35 mm Ø DC 21 mm	119000 21
Carbide core drillDepth of cut 35 mm Ø DC 20 mm	119000 20
Carbide core drillDepth of cut 35 mm Ø DC 17 mm	119000 17
Carbide core drillDepth of cut 35 mm Ø DC 60 mm	119000 60
Carbide core drillDepth of cut 35 mm Ø DC 38 mm	119000 38
Carbide core drillDepth of cut 35 mm Ø DC 55 mm	119000 55
Carbide core drillDepth of cut 35 mm Ø DC 12 mm	119000 12
Carbide core drillDepth of cut 35 mm Ø DC 14 mm	119000 14
Carbide core drillDepth of cut 35 mm Ø DC 16 mm	119000 16
Carbide core drillDepth of cut 35 mm Ø DC 45 mm	119000 45
Carbide core drillDepth of cut 35 mm Ø DC 40 mm	119000 40
Carbide core drillDepth of cut 35 mm Ø DC 28 mm	119000 28
Carbide core drillDepth of cut 35 mm Ø DC 50 mm	119000 50
Carbide core drillDepth of cut 35 mm Ø DC 65 mm	119000 65
Carbide core drillDepth of cut 35 mm Ø DC 24 mm	119000 24
Carbide core drillDepth of cut 35 mm Ø DC 36 mm	119000 36
Carbide core drillDepth of cut 35 mm Ø DC 32 mm	119000 32
Carbide core drillDepth of cut 35 mm Ø DC 18 mm	119000 18
Carbide core drillDepth of cut 35 mm Ø DC 22 mm	119000 22
Carbide core drillDepth of cut 35 mm Ø DC 13 mm	119000 13
Carbide core drillDepth of cut 35 mm Ø DC 35 mm	119000 35
Carbide core drillDepth of cut 35 mm Ø DC 26 mm	119000 26
Carbide core drillDepth of cut 35 mm Ø DC 43 mm	119000 43