

AEG**Impact drill, Type: SB2E850R**

Order data

Order number	075610 SB2E850R
GTIN	4002395294152
Item class	07A

Description

Version:

Powerful **impact drill**

- **Reversible.**
- **Safety shut-off.**
- **FIXTEC metal quick-change chuck.**
- **2-speed planetary gearbox for high torque and optimum adaptation to the material.**

Compact and powerful 850 W impact drill

Advantage:

FIXTEC metal quick-change chuck.

Supplied with:

Metal quick-change chuck 1.5 - 13 mm, additional handle, drilling depth stop, transport case.

Note:

Suitable drill chucks can be found in Group 34.

Technical description

maximum speed 2nd speed	3200 min ⁻¹
maximum vibration to EN	13.7 m/s ²

Power consumption	850 W
Manufacturer's designation	SB2E850R
Weight	2.8 kg
maximum torque	56 Nm
maximum twist drill size Ø in wood	40 mm
maximum twist drill size Ø in steel	13 mm
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 1st speed	1000 min ⁻¹
maximum twist drill size Ø in concrete	20 mm
Packaging	Carrying case
Power supply	Mains operated
Suitable for material	Steel
Suitable for material	Stone
Suitable for material	Concrete
Suitable for material	Masonry
Type of product	Impact drill