



Cordless hammer drill, Type: M12CH4



Order data

Order number	075530 M12CH4
GTIN	4002395004676
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

12 V / 4.0 Ah Li-ion cordless hammer drill with brushless POWERSTATE EC motor, optimised for holes from 4 - 10 mm Ø in concrete and masonry. Redlink Plus electronic – overload protection for long working life of the battery, motor and gearbox.

Advantage:

Brushless POWERSTATE™ motor.

Supplied with:

Supplied with quick charger, 2 × 18V batteries, HD box.

Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Technical description

maximum twist drill size Ø in wood	13 mm
Weight	1.9 kg

maximum twist drill size Ø in steel	10 mm
Manufacturer's designation	M12CH-402X
Battery voltage	12 V
maximum hammer rate	6575 min ⁻¹
maximum vibration to EN	4.4 m/s ²
maximum twist drill size Ø in concrete	13 mm
Tool arbor shape	SDS-plus
Battery capacity	4 Ah
Impact energy	1.1 J
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Modular case (HD=Heavy Duty)
Speed range	0 - 900 min ⁻¹
Shank	SDS Plus
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	Stone
Suitable for material	Concrete
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10
Battery charger Type M1218FC	073840 M1218FC
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10

Li-ion system M12B4 Battery type MB12	073815 MB12
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drilllong with SDS-plus shank socket Drill Ø 12 mm	787060 12
Battery charger Type M1218C	073840 M1218C
Carbide-tipped multi-purpose drilllong with SDS-plus shank socket Drill Ø 8 mm	787060 8
Carbide-tipped multi-purpose drill setlong Drill Ø 6-12 mm	787055 6-12