




Indexable drill toolholder VARIA, V5, Clamping range \varnothing D1: 10mm



Order data

Order number	319829 10
GTIN	2050001077943
Item class	33E

Description

Advantage:

- **Quick change using a single clamping point, therefore tool change without risk of injury.**
- **Cutter tools lie pre-set at the machine.**
- **Compact design - low unit costs.**

Application:

For clamping tools with drive flats.

Note:

Maximum tightening torque for VX3 and VX4 is 5.7 Nm, which can be achieved using the appropriate torque screwdriver No. 211750 size 5.7. Maximum tightening torque for V5 is 10 Nm. When releasing the deposits, do not travel beyond the stop.

Extra short version available on request. We recommend the EWS Clean and cleaning set for cleaning the Varia toolholders and replaceable inserts.

Technical description

Overhang dimension A	29 mm
Clamping \varnothing D ₁	10 mm
External \varnothing D	35 mm
Adapter	V5

Type of product

Side lock arbor