



Universal soldering iron Multi-TC with temperature control, Heating power: 75 W



Order data

Order number	082150 75
GTIN	4003008065664
Item class	04C

Description

Version:

Powerful general-purpose soldering iron with a precisely regulated temperature sensor located directly below the internally heated soldering tip. The combination of this direct temperature measurement with the precise control electronics integrated in the handle enables the **most delicate soldering jobs** to be professionally done on sensitive electronic components **and also applications with very high thermal requirements.**

Application:

For mobile use in the field of service, maintenance and repairs. The ERSA Multi-TC has the functionality of a large soldering station, but no galvanic separation.

Heating power: 285 W

Warm-up time: approx. 34 s

Heating power: 75 W

Control range of soldering tip temperature: 250 - 450 °C

Weight without power lead: 60 g

Technical description

Heating power	285 W
Heating power	75 W
Control range of soldering tip temperature	250 - 450 °C
Weight without power lead	60 g
Warm-up time	approx. 34 s
Power supply	Mains operated
Type of product	Soldering iron

Accessories

Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1,5 mm	082365 1,5
Solder wire Sn60Pb40 roll of 250g Soldering wire Ø 1 mm	082360 1
Desoldering pump PDD03 plastic, antistatic	082355
Solder wire Sn60Pb40 roll of 250g Soldering wire Ø 1,5 mm	082360 1,5
Soldering tip Manufacturer's designation BDLF	082400 BDLF
Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1 mm	082365 1
Holder	0A18
Soldering tip ERSADUR, 2.2mm/0.087in	0842CD/SB