



Compact angle grinder, Type: 722178



Order data

Order number	077111 722178
GTIN	4014586875323
Item class	03F

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: WSG 15-125P

Power consumption: 1500 W

maximum speed: 11,000 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 33 mm

Weight: 2.3 kg

Technical description

maximum cutting depth	33 mm
-----------------------	-------

Restart block	yes
maximum disc Ø	125 mm
Special features	Short body
maximum speed	11,000 min ⁻¹
Dead man's circuit	no
Weight	2.3 kg
maximum vibration to EN	5 m/s ²
Power consumption	1500 W
Manufacturer's designation	WSG 15-125P
Power supply	Mains operated
Type of product	Angle grinder