

**Clamping head smooth, Top 65, Clamping  $\varnothing$  (0.5 mm increments): 32mm****Order data**

Order number	329970 32
GTIN	2050001927255
Item class	33H

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

**Advantage:**

- **25% greater clamping force than clamping head RD.**
- **No radial movement between clamping head and clamping element mounting, therefore immune to dirt.**
- **Unique stiffness due to large seating area of the clamping segments.**

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Recommendation:**

**Clamping heads for special profiles to your individual requirements on request.**

**Note:**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Clamping $\varnothing$	32 mm
------------------------	-------

Profile	round
Hardness	60 HR
Clamping face	smooth
Length L	49 mm
Adapter	Top 65
Type of product	Clamping head