

mato

Pneumatic grease gun, 400 g



Order data

Order number	083585
GTIN	4016553410056
Item class	08H

Description

Version:

One-handed pneumatic grease guns, outstandingly well balanced. **Single-shot system for optimum grease management (1 cm³ / stroke)**, pressure ratio 1:60.

Refilling with loose grease (contents: 500 cm³) or cartridges (contents: 400 g).

Suitable for greases up to NLGI 2.

Supplied with:

Rubberised armoured hose, 4-jaw hydraulic push-on connector.

Working pressure: 400 bar

Test pressure: 800 bar

Hose connection thread: R1/8 inch

Operational range compressed air supply: 3 - 8 bar

Technical description

Test pressure	800 bar
Operational range compressed air supply	3 - 8 bar
Hose connection thread	R1/8 inch
Working pressure	400 bar
Product name attribute	400 g

Accessories

4-jaw hydraulic push-on connector safeLOCK Connection thread 1/8	083596 1/8
Multi-purpose grease cartridge for Standard grease guns Type PLUS	083590 PLUS
Nozzle with conical connector Connection thread 1/8	083584 1/8
4-jaw hydraulic push-on connector Connection thread 1/8	083589 1/8
Nozzle with universal connector Connection thread 1/8	083583 1/8
Multi-purpose grease cartridge for Lube-Shuttle® grease guns Type UNI	083592 UNI
Multi-purpose grease cartridge for Standard grease guns Type UNI	083590 UNI
Multi-purpose grease cartridge for Lube-Shuttle® grease guns Type PLUS	083592 PLUS
Armoured hose with 4-jaw hydraulic push-on connector Connection thread 1/8	083586 1/8
Armoured hose with push-on connector Connection thread 1/8	083588 1/8