

SWISS TOOLS

Toolholder axial triple, right-hand, PSC 63, for toolholder square: 20mm**Order data**

Order number	318872 20
GTIN	2050001672636
Item class	36D

Description**Version:**

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request.

Technical description

Overhang dimension A	125 mm
Clamping length L ₁	95 mm
for toolholder square	20 mm
B	30 mm
External Ø D	90 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice

