

SWISS TOOLS

**Boring bar holder, PSC 40, Clamping range  $\varnothing$  D1: 10mm****Order data**

Order number	318886 10
GTIN	2050001714619
Item class	36D

**Description****Application:**

For use on lathes and milling centres.  
For mounting boring bars.

**Note:**

PSC clamping stud on request.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	10 mm
Overhang dimension A	65 mm
L <sub>1</sub>	43 mm
External $\varnothing$ D	34 mm
Adapter	PSC 40
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

