

SWISS TOOLS

Boring bar holder, PSC 63, Clamping range \varnothing D1: 6mm**Order data**

Order number	318888 6
GTIN	2050001672889
Item class	36D

Description**Application:**

For use on lathes and milling centres.
For mounting boring bars.

Note:

PSC clamping stud on request.

Technical description

Clamping \varnothing D ₁	6 mm
Overhang dimension A	80 mm
L ₁	58 mm
External \varnothing D	34 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

