

SWISS TOOLS

Toolholder axial triple, right-hand, PSC 63, for toolholder square: 25mm



Order data

Order number	318872 25
GTIN	2050001673435
Item class	36D

Description

Version:

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request.

Technical description

for toolholder square	25 mm
Clamping length L ₁	102 mm
Overhang dimension A	130 mm
B	40 mm
External Ø D	102 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice

