

 kurtz ersa

## Quick soldering iron Multi-Sprint, ERSA Type: 960ED



### Order data

Order number	082200 960ED
GTIN	4003008060829
Item class	04C

### Description

#### Version:

Unusually light soldering gun without transformer; with PTC heating element. **Warm-up time approx. 20 sec.** Periodic pressing of the trigger allows heat output to be matched to the heat requirements of the joint. High efficiency internally heated soldering tip. Power cable 1.5 m.

#### Application:

Particularly useful for assembly and repair work, because of its **working range of 15 – 100 W** (used as standard soldering iron).

Soldering tip width: 3.2 mm

Heating power: 150 W

Heating power: 75 W

Soldering tip temperature after 3 minutes: 350 °C

Weight without power lead: 100 g

### Technical description

Soldering tip temperature after 3 minutes	350 °C
Heating power	150 W
Soldering tip width	3.2 mm
Heating power	75 W

Weight without power lead	100 g
ERSA type	960ED
Power supply	Mains operated
Type of product	Soldering iron

## Accessories

Soldering tip Manufacturer's designation 832CDLF	082400 832CDLF
Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1 mm	082365 1
Solder wire Sn60Pb40 roll of 250g Soldering wire Ø 1 mm	082360 1
Soldering tip Manufacturer's designation BDLF	082400 BDLF
Desoldering pump PDD03 plastic, antistatic	082355
Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1,5 mm	082365 1,5
Soldering tip Manufacturer's designation 832EDLF	082400 832EDLF
Solder wire Sn60Pb40 roll of 250g Soldering wire Ø 1,5 mm	082360 1,5
Soldering tip Manufacturer's designation 832SDLF	082400 832SDLF
Holder	0A18
Soldering tip ERSADUR, 3.2mm/0.126in	0832EDLF/SB