

SWISS TOOLS

**Toolholder axial, single, right-hand, HSK-T 63, for toolholder square: 20mm****Order data**

Order number	318802 20
GTIN	2050001673060
Item class	36D

**Description****Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Technical description**

Clamping length $L_1$	45 mm
Overhang dimension A	90 mm
for toolholder square	20 mm
B	30 mm
External $\varnothing$ D	80 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Pin vice

