

SWISS TOOLS

Toolholder axial, single, right-hand, HSK-T 63, for toolholder square: 25mm**Order data**

Order number	318802 25
GTIN	2050001673077
Item class	36D

Description**Version:**

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Technical description

Overhang dimension A	100 mm
Clamping length L ₁	58 mm
for toolholder square	25 mm
B	40 mm
External Ø D	102 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Pin vice

