

SWISS TOOLS

Boring bar holder, PSC 40, Clamping range \varnothing D1: 20mm**Order data**

Order number	318886 20
GTIN	2050001714640
Item class	36D

Description**Application:**

For use on lathes and milling centres.
For mounting boring bars.

Note:

PSC clamping stud on request.

Technical description

Clamping \varnothing D ₁	20 mm
L ₁	43 mm
Overhang dimension A	65 mm
External \varnothing D	44 mm
Adapter	PSC 40
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

