

SWISS TOOLS

**Toolholder diagonal 45°, right-hand, PSC 63, for toolholder square: 20mm**

**Order data**

Order number	318880 20
GTIN	
Item class	36D

**Description**
**Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Note:**

PSC clamping stud on request.

Through-coolant: yes

Overhang dimension A: 100 mm

B: 30 mm

External Ø D: 80 mm

Tip centre offset f: 15 mm

**Technical description**

for toolholder square	20 mm
Tip centre offset f	15 mm
Overhang dimension A	100 mm
B	30 mm
External Ø D	80 mm
Adapter	PSC 63

Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice