

SWISS TOOLS

**Toolholder diagonal 45°, right-hand, PSC 63, for toolholder square: 25 mm**

**Order data**

Order number	318880 25
GTIN	2050001672858
Item class	36D

**Description**
**Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Note:**

PSC clamping stud on request.

Through-coolant: yes

Overhang dimension A: 110 mm

B: 40 mm

External  $\varnothing$  D: 102 mm

Tip centre offset f: 15 mm

**Technical description**

Overhang dimension A	110 mm
for toolholder square	25 mm
B	40 mm
Tip centre offset f	15 mm
External $\varnothing$ D	102 mm
Adapter	PSC 63

Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Steel toolholder