

SWISS TOOLS

Boring bar holder, HSK-T 63, Clamping range \varnothing D1: 16mm**Order data**

Order number	318830 16
GTIN	2050001672735
Item class	36D

Description**Application:**

For mounting boring bars.
For use on lathes and milling centres.

Technical description

Overhang dimension A	75 mm
L ₁	49 mm
Clamping \varnothing D ₁	16 mm
External \varnothing D	40 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Side lock arbor