



Value pack thread sealant, 5 pieces



Order data

Order number	GG3322 58-11
GTIN	
Item class	GGN

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

Medium-strength pipe and thread sealant, NSF-P1 approved, **carries no hazard labels**.

Supplied with:

5 × thread sealant, 50 ml, No. 083322 58-11.

Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

Technical description

for imperial thread size	2 in
for thread size M to	M56

Data sheet

Flashpoint	100 °C
Operating temperature range	-55 - 150 °C
Dynamic viscosity	20000 - 80000 mPas
Suitable for material	Metal
Chemical basis	anaerobic methacrylate
Working life after date of manufacture	12 mo
Disassembly	with special tool
Colour	yellow
Shape	liquid
Functional strength to	1 - 2 h
Strength class	medium strength
Manufacturer's designation	58-11
Capacity	50 ml
Density	1.1 g/cm ³
Touch dry after	15 - 30 min
Suitable for application area	all screw fastenings
Storage temperature	10 - 25 °C
for thread types	All
Maximum gap size	0.3 mm
minimum break-away torque	18 - 24 Nm
Product name attribute	50 ml
Type of product	Sealant

Suitable products

No Shop URL available for: GG3322 58-11