

SWISS TOOLS

## Toolholder axial, double, right-hand, HSK-T 63, for toolholder square: 20 mm



### Order data

Order number	318811 20
GTIN	2050001673107
Item class	36D

### Description

#### Version:

With adjustable cooling nozzle with internal thread.

#### Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Through-coolant: yes

Overhang dimension A: 90 mm

Clamping length  $L_1$ : 45 mm

B: 30 mm

External  $\varnothing$  D: 80 mm

### Technical description

Overhang dimension A	90 mm
for toolholder square	20 mm
B	30 mm
Clamping length $L_1$	45 mm
External $\varnothing$ D	80 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3

Through-coolant	yes
Type of product	Steel toolholder