

SWISS TOOLS

Toolholder axial single, left-hand, PSC 63, for toolholder square: 20mm**Order data**

Order number	318864 20
GTIN	2050001673411
Item class	36D

Description**Version:**

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request.

Technical description

Clamping length L_1	75 mm
Overhang dimension A	100 mm
B	30 mm
for toolholder square	20 mm
External \varnothing D	80 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice

