

SWISS TOOLS

Boring bar holder, PSC 50, Clamping range \varnothing D1: 10mm**Order data**

Order number	318887 10
GTIN	2050001714671
Item class	36D

Description**Application:**

For use on lathes and milling centres.
For mounting boring bars.

Note:

PSC clamping stud on request.

Technical description

L ₁	48 mm
Clamping \varnothing D ₁	10 mm
Overhang dimension A	70 mm
External \varnothing D	34 mm
Adapter	PSC 50
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

