

SWISS TOOLS

**Toolholder axial single, left-hand, PSC 63, for toolholder square: 25mm****Order data**

Order number	318864 25
GTIN	2050001673428
Item class	36D

**Description****Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Note:**

PSC clamping stud on request.

**Technical description**

Overhang dimension A	130 mm
for toolholder square	25 mm
Clamping length L <sub>1</sub>	102 mm
B	40 mm
External Ø D	102 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice

