



Gas soldering kit Independent, ERSA Type: 75



Order data

Order number	082250 75
GTIN	4003008061574
Item class	04C

Description

Version:

Ergonomic gas soldering iron with **easy to use piezo ignition**. Requires commercially available butane gas (as for gas lighters).

Application:

For maintenance and repair work, in particular where no power supply is available or the power has been switched off.

Supplied with:

Chisel-shaped soldering tips 1.0, 2.4, 3.2, and 4.8 mm. Flame nozzle (up to maximum 1400 °C), hot gas nozzle (up to max. 700 °C), soldering tip, reflector plate for applying shrink sleeving, cleaning sponge and sponge holder, in a handy plastic case.

Soldering tip width: 1 - 4.8 mm

Warm-up time: approx. 46 s

Heating power steplessly adjustable: 15 - 75 W

maximum soldering tip temperature: 580 °C

Operating life per gas filling: 30 - 90 min

Weight of the gas-heated soldering iron: 73 g

Technical description

Weight of the gas-heated soldering iron	73 g
Operating life per gas filling	30 - 90 min
Type of ignition	Piezo ignition
Warm-up time	approx. 46 s

maximum soldering tip temperature	580 °C
Heating power steplessly adjustable	15 - 75 W
Soldering tip width	1 - 4.8 mm
Type of gas	Butane gas
Type of product	Soldering iron

Accessories

Soldering tip Manufacturer's designation G072KN	082400 G072KN
Box for sponge	0G156
Flame nozzle	0G072BE/SB
Soldering tip, 4.8mm/1.189in	0G072VN/SB
Soldering tip, 3.2mm/0.126in	0G072AN/SB
Hot gas nozzle	0G072HE/SB
Soldering tip, 1.0mm/0.039in	0G072CN/SB
Soldering tip, 2.4mm/0.094in	0G072KN/SB
Hot blade	0G072MN/SB
Deflector for hot gas nozzle	0G072RE/SB