

AEG

Impact drill, Manufacturer's designation: ERGOMAX



Order data

| | |
|--------------|----------------|
| Order number | 075610 ERGOMAX |
| GTIN | 4002395198870 |
| Item class | 07A |

Description

Version:

Powerful **impact drill**

- **Reversible.**
- **Safety shut-off.**
- **FIXTEC metal quick-change chuck.**
- **2-speed planetary gearbox for high torque and optimum adaptation to the material.**
- **Impact drill, unique design, outstandingly well balanced for universal applications.**
- **Highest torque in its class.**
- **Demountable rear handle.**

Supplied with:

Metal quick-change chuck 1.5 - 13 mm, additional handle, drilling depth stop, transport case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Suitable drill chucks can be found in Group 34.

Packaging: Carrying case

Manufacturer's designation: ERGOMAX

Power consumption: 750 W

maximum torque: 58 N·m

maximum speed 1st speed: 1200 rpm

maximum speed 2nd speed: 3400 rpm
maximum twist drill size Ø in steel: 13 mm

Technical description

| | |
|--|---------------------|
| maximum twist drill size Ø in wood | 40 mm |
| maximum speed 2nd speed | 3400 rpm |
| maximum vibration to EN | 32 m/s ² |
| maximum twist drill size Ø in concrete | 20 mm |
| Quick-clamping chuck range | 1.5 - 13 mm |
| Power consumption | 750 W |
| maximum twist drill size Ø in steel | 13 mm |
| maximum speed 1st speed | 1200 rpm |
| Manufacturer's designation | ERGOMAX |
| Weight | 2.6 kg |
| maximum torque | 58 N·m |
| Packaging | Carrying case |