


Toolholder, form B1 radial right-hand, short, Shank \varnothing d1: 40 mm

Order data

Order number	319000 40
GTIN	4045197191007
Item class	32V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 25 mm

h_2 : 34 mm

b_1 : 85 mm

b_2 : 42.5 mm

h_5 : 48 mm

h_6 : 42.5 mm

Technical description

l_1	22 mm
l_2	44 mm

b ₂	42.5 mm
h ₁	25 mm
Colour code for VDI shanks	VDI 40
h ₅	48 mm
Shank Ø D ₁	40 mm
b ₁	85 mm
h ₆	42.5 mm
h ₂	34 mm
Shape	B
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------