



## Toolholder form B2 radial left-hand, short, Shank $\varnothing$ d1: 50 mm



### Order data

Order number	319010 50
GTIN	4045197373663
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

#### Application:

Mainly for external machining.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

$h_1$ : 32 mm

$h_2$ : 41 mm

$b_1$ : 100 mm

$b_2$ : 50 mm

$h_5$ : 35 mm

$h_6$ : 60 mm

### Technical description

$b_2$	50 mm
$h_1$	32 mm

$h_2$	41 mm
$h_5$	35 mm
$h_6$	60 mm
$l_2$	55 mm
$l_1$	30 mm
Shank $\varnothing D_1$	50 mm
Colour code for VDI shanks	VDI 50
$b_1$	100 mm
Shape	B
Type of product	VDI tool arbor