

SWISS TOOLS

## Toolholder axial double, right-hand, PSC 50, for toolholder square: 20 mm



### Order data

Order number	318923 20
GTIN	2050001715531
Item class	36D

### Description

**Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Note:**

PSC clamping stud on request.

Arbor standard: ISO 26623-2

Through-coolant: true

Overhang dimension A: 98 mm

Clamping length  $L_1$ : 75 mm

B: 30 mm

External  $\varnothing$  D: 80 mm

### Technical description

for toolholder square	20 mm
Clamping length $L_1$	75 mm
B	30 mm
Overhang dimension A	98 mm
External $\varnothing$ D	80 mm
Adapter	PSC 50

Arbor standard	ISO 26623-2
Through-coolant	yes