

SWISS TOOLS

Boring bar holder, PSC 63, Clamping range \varnothing D1: 25mm**Order data**

Order number	318888 25
GTIN	2050001672940
Item class	36D

Description**Application:**

For use on lathes and milling centres.
For mounting boring bars.

Note:

PSC clamping stud on request.

Technical description

Clamping \varnothing D ₁	25 mm
Overhang dimension A	100 mm
L ₁	78 mm
External \varnothing D	50 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

